

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable



1543692

<https://www.phoenixcontact.com/us/products/1543692>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, gray RAL 7001, Socket straight M8, coding: A, on Socket angled M8, cable length: 30 m

Commercial data

Item number	1543692
Packing unit	5 pc
Minimum order quantity	50 pc
Product key	AF1BBA
GTIN	4046356101813
Weight per piece (including packing)	856.16 g
Weight per piece (excluding packing)	856.16 g
Country of origin	PL

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable



1543692

<https://www.phoenixcontact.com/us/products/1543692>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Socket straight M8
Number of positions	3
Coding type	A

Connection 2

Type	Socket angled M8
Number of positions	3

Cable/line


Cable length	30 m
--------------	------

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable

1543692

<https://www.phoenixcontact.com/us/products/1543692>

PVC gray [500]

Dimensional drawing	
Cable weight	29 kg/km
Number of positions	3
Shielded	no
Cable type	PVC gray [500]
Conductor type	Assembled shielded round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	3x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≥ 300 V
Test voltage	≤ 3000 V
Smallest bending radius, fixed installation	13 mm
Halogen-free	no
Flame resistance	As per UL-Style 2464
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable



1543692

<https://www.phoenixcontact.com/us/products/1543692>

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable

1543692

<https://www.phoenixcontact.com/us/products/1543692>


Drawings

Dimensional drawing



Socket M8 x 1, straight

Dimensional drawing




Socket M8 x 1, straight

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable

1543692


<https://www.phoenixcontact.com/us/products/1543692>

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable



1543692
<https://www.phoenixcontact.com/us/products/1543692>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

SAC-3P-M 8FS/30,0-500/M 8FS - Sensor/actuator cable



1543692

<https://www.phoenixcontact.com/us/products/1543692>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com