

HC-M-KV-M40(27-34) - Cable gland



1607729

<https://www.phoenixcontact.com/us/products/1607729>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Metal screw connection up to 5 bar, thread length: 8 mm, cable diameter: 27 ... 34 mm, WAF 50, screw connection: M40

Commercial data

Item number	1607729
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DAX
Catalog page	Page 690 (C-4-2015)
GTIN	4017918938819
Weight per piece (including packing)	184.2 g
Weight per piece (excluding packing)	168.65 g
Customs tariff number	74198090
Country of origin	DE

HC-M-KV-M40(27-34) - Cable gland

1607729

<https://www.phoenixcontact.com/us/products/1607729>




Technical data

Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Type of the screw connection	M40
Manufacturer	Jacob
Manufacturer Designation	101036M40
Shielded	no

Dimensions

Dimensional drawing	
Length	35 mm
Length of the connecting thread	8 mm
Hole diameter	40.1 mm ... 40.3 mm
Wrench size, union nut	50 mm
Wrench size, support	50 mm
Hexagon angular dimension	58 mm
Thread type connection side	M40 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	20 Nm (Union nut)
	20 Nm (Support sleeve)

Material specifications

Material Compression ring	PA
Seal material O-ring	NBR
Seal material Cable seal	Neoprene
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter Cable 1	27 mm ... 34 mm
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (up to 5 bar)
----------------------	--------------------

HC-M-KV-M40(27-34) - Cable gland

1607729

<https://www.phoenixcontact.com/us/products/1607729>



Ambient temperature (operation)	-30 °C ... 100 °C
---------------------------------	-------------------

HC-M-KV-M40(27-34) - Cable gland


1607729

<https://www.phoenixcontact.com/us/products/1607729>



Drawings

Dimensional drawing



Dimensional drawing

HC-M-KV-M40(27-34) - Cable gland

1607729

<https://www.phoenixcontact.com/us/products/1607729>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607729>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

HC-M-KV-M40(27-34) - Cable gland



1607729

<https://www.phoenixcontact.com/us/products/1607729>

Classifications

ECLASS

ECLASS-13.0	27140801
-------------	----------

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

HC-M-KV-M40(27-34) - Cable gland



1607729

<https://www.phoenixcontact.com/us/products/1607729>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fb259922-836a-4076-b45a-ad83019743f0

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com