

VS-09-BU-DSUB/9-MPT-0,5 - D-SUB contact insert



1688395

<https://www.phoenixcontact.com/us/products/1688395>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB contact insert, shell size 1, with 9 signal contacts, female type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection

Your advantages

- Easy connection with screw terminal technology

Commercial data

Item number	1688395
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918817534
Weight per piece (including packing)	13.98 g
Weight per piece (excluding packing)	13.98 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	9
Connection profile	D-SUB
Number of slots	1
Type	Socket
Shielded	yes

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	60 V
Rated current	5 A
Insulation resistance	$\geq 5000 \text{ M}\Omega$
Contact resistance per contact pair	$\leq 2.5 \text{ m}\Omega$
Transmission medium	Copper
Power transmission	Power

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Width	31 mm
Height	12.6 mm
Length	49 mm

Material specifications

Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 200
Insertion force per signal contact	$\leq 3.30 \text{ N}$
Extraction force per signal contact	$\leq 2.2 \text{ N}$

Environmental and real-life conditions

VS-09-BU-DSUB/9-MPT-0,5 - D-SUB contact insert



1688395

<https://www.phoenixcontact.com/us/products/1688395>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-09-BU-DSUB/9-MPT-0,5 - D-SUB contact insert



1688395

<https://www.phoenixcontact.com/us/products/1688395>

Classifications

ECLASS

ECLASS-13.0	27440302
-------------	----------

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5a30f7cf-9ebd-464a-9e6c-0862b2a39edf