

# FBR 10-5-EX - Fixed bridge

2303226

<https://www.phoenixcontact.com/us/products/2303226>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fixed bridge, pitch: 5 mm, number of positions: 10, color: silver-colored

## Commercial data

Item number	2303226
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918108892
Weight per piece (including packing)	15.36 g
Weight per piece (excluding packing)	14.27 g
Customs tariff number	85369095
Country of origin	PL

# FBR 10-5-EX - Fixed bridge

2303226

<https://www.phoenixcontact.com/us/products/2303226>



## Technical data

### Product properties

Product type	Screw bridge
Number of positions	10
Pitch	5 mm

### Dimensions

Pitch	5 mm
-------	------

### Material specifications

Color	silver-colored
Material	Copper

### Mounting

Mounting type	Screw mounting
---------------	----------------

# FBR 10-5-EX - Fixed bridge

2303226

<https://www.phoenixcontact.com/us/products/2303226>



## Classifications

### ECLASS

ECLASS-13.0	27250303
-------------	----------

### ETIM

ETIM 9.0	EC000489
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FBR 10-5-EX - Fixed bridge

2303226

<https://www.phoenixcontact.com/us/products/2303226>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)