

# ME MAX 17,5 PLATE BK - Insertion plate



2707288

<https://www.phoenixcontact.com/us/products/2707288>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 14.2 mm, height: 73.6 mm, depth: 1 mm, color: black (similar RAL 9005)



## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2707288
Packing unit	200 pc
Minimum order quantity	200 pc
Product key	ACHABZ
GTIN	4017918897611
Weight per piece (including packing)	1.181 g
Weight per piece (excluding packing)	1.155 g
Country of origin	DE

# ME MAX 17,5 PLATE BK - Insertion plate



2707288

<https://www.phoenixcontact.com/us/products/2707288>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 17,5..
Type	Insertion plate
Ventilation openings present	no

### Dimensions

Width	14.2 mm
Height	73.6 mm
Depth	1 mm

### Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### PCB data

Type of PCB mount	Latching
-------------------	----------

### Mounting

Mounting type	Slot
---------------	------

# ME MAX 17,5 PLATE BK - Insertion plate



2707288

<https://www.phoenixcontact.com/us/products/2707288>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2707288>



**UL Recognized**

Approval ID: E240868

# ME MAX 17,5 PLATE BK - Insertion plate



2707288

<https://www.phoenixcontact.com/us/products/2707288>

## Classifications

### ECLASS

ECLASS-13.0	27190605
-------------	----------

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX 17,5 PLATE BK - Insertion plate



2707288  
<https://www.phoenixcontact.com/us/products/2707288>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)