

D-UK 3-MSTB - End cover

3002047

<https://www.phoenixcontact.com/us/products/3002047>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, color: gray, product range: DECKEL + RZ + DP, width: 2.5 mm



Commercial data

Item number	3002047
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4017918090067
Weight per piece (including packing)	2.17 g
Weight per piece (excluding packing)	2.099 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Product properties

Product type	End cover
Product family	DECKEL + RZ + DP
Number of positions	1
Pitch	0 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C

Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

Dimensions

Width	2.5 mm
Height	47 mm
Length	42.5 mm
Pitch	0 mm

D-UK 3-MSTB - End cover

3002047

<https://www.phoenixcontact.com/us/products/3002047>



Classifications

ECLASS

ECLASS-13.0	27250301
-------------	----------

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%