

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PVC, black RAL 9005, free cable end, on Socket straight M12, coding: A, cable length: 10 m, Without PATGs

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

Item number	1422723
Packing unit	1 pc
Minimum order quantity	100 pc
Product key	AF1CKA
GTIN	4055626312347
Weight per piece (including packing)	525 g
Weight per piece (excluding packing)	520 g
Country of origin	PL

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	8
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	2 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M12
Number of positions	8
Coding type	A

Cable/line

Cable length	10 m
--------------	------

PVC black [PVC]

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Dimensional drawing	
Cable weight	54 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	8
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	8x 0.25 mm² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.23 mm
Thickness, outer sheath	≥ 0.76 mm
Overall twist	8 wires around filler to the core
Max. conductor resistance	79 Ω/km (at 20 °C)
Insulation resistance	≥ 200 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Flame resistance	as per VW-1 in accordance with UL 758
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP68

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable

1422723

<https://www.phoenixcontact.com/us/products/1422723>


Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side


SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Circuit diagram



Contact assignment of the M12 socket

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723
<https://www.phoenixcontact.com/us/products/1422723>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

SAC-8P-10,0-PVC/M12FS OBS - Sensor/actuator cable



1422723

<https://www.phoenixcontact.com/us/products/1422723>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
-------------------------------------	----------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com