

FL NP PND-4TX PB - Proxy



2985071

<https://www.phoenixcontact.com/us/products/2985071>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Proxy for PROFINET-RT, PROFIBUS proxy with integrated 4-port switch, for use with PC WORX only

Product description

The PROFIBUS proxy opens up a new PROFIBUS world for our controller landscape. All PROFIBUS devices can be addressed via the proxy from every PROFINET-capable controller. The engineering is perfectly integrated into PC WORX. The PROFIBUS diagnostics are mapped completely by PROFINET mechanisms.

Your advantages

- Data exchange, diagnostics, and parameterization are via the PROFINET protocol
- LLDP support for topology detection
- PROFINET update rates = 1 ms
- Can be integrated and parameterized in any controller using the PROFINET functionality

Commercial data

Item number	2985071
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR14
Product key	DREBAB
GTIN	4046356163545
Weight per piece (including packing)	720.4 g
Weight per piece (excluding packing)	720.1 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Product properties

Product type	Gateways/Proxies
Type	Stand-alone

System properties

INTERBUS-Master

Number of supported devices	max. 125
-----------------------------	----------

Electrical properties

Maximum power dissipation for nominal condition	8.4 W
---	-------

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	18.5 V DC ... 30.2 V DC
Typical current consumption	350 mA

Interfaces

Ethernet

Connection method	RJ45 jack
Transmission speed	10/100 Mbps
No. of channels	4

PROFIBUS DP V0/V1 class 2 master

Connection method	9-pos. D-SUB socket
Transmission speed	to 12 Mbps
No. of channels	1

Dimensions

Width	128 mm
Height	95 mm
Depth	69 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

FL NP PND-4TX PB - Proxy

2985071

<https://www.phoenixcontact.com/us/products/2985071>



Classifications

UNSPSC

UNSPSC 21.0	43222609
-------------	----------

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com