

PATO 1/30 - Conductor marker carrier



0822495

<https://www.phoenixcontact.com/us/products/0822495>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent, unmarked, cable diameter range: 2 ... 3.5 mm, mounting type: clip on, text field height: 4 mm, text field width: 30 mm

Your advantages

- Can be labeled using UC-WMT ... or US-WMT ... plastic labels or the EMT ... insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired

Commercial data

Item number	0822495
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BG12
Product key	BG221A
GTIN	4046356326179
Weight per piece (including packing)	0.666 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	30 mm
Height	5.6 mm
Depth	8.2 mm

Material specifications

Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Cable/line

External cable diameter	2 mm ... 3.5 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	clip on
---------------	---------

PATO 1/30 - Conductor marker carrier



0822495

<https://www.phoenixcontact.com/us/products/0822495>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATO 1/30 - Conductor marker carrier



0822495

<https://www.phoenixcontact.com/us/products/0822495>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.005 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com