

US-EMSP (90X60) SR - Device marker



0828932

<https://www.phoenixcontact.com/us/products/0828932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device marker, Card, silver, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: screw, rivet, Number of individual labels: 2, text field height: 60 mm, text field width: 90 mm

Your advantages

- The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- The perforated markers and labels are easy to separate and can be easily fitted
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The sheets provide space for including function texts
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD

Commercial data

Item number	0828932
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356559737
Weight per piece (including packing)	14.97 g
Weight per piece (excluding packing)	13.672 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	2
Number of individual labels per row	1
Identification technology	Thermal transfer for sheets and cards, UV LED technology

Mounting

Mounting type	screw, rivet
---------------	--------------

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	silver
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	100.00 mm
Height	60.00 mm
Depth	0.50 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMSP (90X60) SR - Device marker



0828932

<https://www.phoenixcontact.com/us/products/0828932>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EMSP (90X60) SR - Device marker



0828932

<https://www.phoenixcontact.com/us/products/0828932>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com