

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, gray RAL 7001, Plug straight M12, coding: A, on Plug straight M8, cable length: 0.6 m

Commercial data

Item number	1401015
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CCA
GTIN	4046356517256
Weight per piece (including packing)	29.72 g
Weight per piece (excluding packing)	29.72 g
Country of origin	PL

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12
Number of positions	4
Coding type	A

Connection 2

Type	Plug straight M8
------	------------------

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015


<https://www.phoenixcontact.com/us/products/1401015>

Number of positions	4
---------------------	---

Cable/line

Cable length	0.6 m
--------------	-------

PVC gray [500]

Dimensional drawing	
Cable weight	33 kg/km
Number of positions	4
Shielded	no
Cable type	PVC gray [500]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	4x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, green-yellow
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable




1401015

<https://www.phoenixcontact.com/us/products/1401015>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M8 x 1 male plug, straight version


SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side


SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015


<https://www.phoenixcontact.com/us/products/1401015>

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Circuit diagram



Contact assignment of the M12 plug

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M12MS/0,6-500/M8MS DVS - Sensor/actuator cable



1401015

<https://www.phoenixcontact.com/us/products/1401015>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com