

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, black RAL 9005, shielded, free cable end, on Socket angled M12, coding: A, cable length: 10 m, Customer version

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1403413
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CJA
GTIN	4046356651646
Weight per piece (including packing)	546.9 g
Weight per piece (excluding packing)	546 g
Country of origin	PL

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket angled M12
Number of positions	4
Coding type	A

Cable/line

Cable length	10 m
--------------	------


PVC black [PVC]

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Dimensional drawing	
Cable weight	52 kg/km
Number of positions	4
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.4 mm ±0.02 mm
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Optical shield covering	85 %
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	in accordance with DIN EN 60811-2-1
Special properties	Free of substances which would hinder coating with paint or varnish Silicone-free
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413
<https://www.phoenixcontact.com/us/products/1403413>

Degree of protection	IP65
	IP67

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Drawings

Dimensional drawing



M12 x 1 socket, angled, shielded

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Diagram




SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Circuit diagram



Contact assignment of the M12 socket

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413

<https://www.phoenixcontact.com/us/products/1403413>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-10-PVC/M12FR SH OBS VA - Sensor/actuator cable



1403413
<https://www.phoenixcontact.com/us/products/1403413>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	8.434 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com