

1405749
<https://www.phoenixcontact.com/us/products/1405749>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet, 8-position, shielded, Plug straight M12 SPEEDCON, on Plug straight RJ45, cable length: 0.2 m

Commercial data

Item number	1405749
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CMI
GTIN	4046356753975
Weight per piece (including packing)	39.4 g
Weight per piece (excluding packing)	39.4 g
Country of origin	PL

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	8

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC

Material specifications

Outer sheath, material	PUR
------------------------	-----

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Locking type	SPEEDCON

Connection 2

Type	Plug straight RJ45
------	--------------------

Cable/line

Cable length	0.2 m
Signal type/category	Ethernet
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021

SAC-MS/0,2-94B/R4AC SCO - Network cable



1405749

<https://www.phoenixcontact.com/us/products/1405749>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com