

NBC-MSD/3,0-937/R4AQ 4ME4 FI - Network cable



1415854

<https://www.phoenixcontact.com/us/products/1415854>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), 4-pos., RADOX® GKW, RAL 9005 (black), shielded, straight M12 SPEEDCON/IP67 connector (D-coding) to straight RJ45/IP20 QUICKON connector, cable length: 3 m, customer version

Commercial data

Item number	1415854
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJN
GTIN	4055626054124
Weight per piece (including packing)	229.8 g
Weight per piece (excluding packing)	222.77 g
Country of origin	PL

NBC-MSD/3,0-937/R4AQ 4ME4 FI - Network cable



1415854

<https://www.phoenixcontact.com/us/products/1415854>

Technical data

Product properties

Product type	Data cable preassembled
--------------	-------------------------

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

NBC-MSD/3,0-937/R4AQ 4ME4 FI - Network cable



1415854

<https://www.phoenixcontact.com/us/products/1415854>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------