

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable



1505180

<https://www.phoenixcontact.com/us/products/1505180>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR/PVC, green RAL 6017, Plug angled M12, coding: A, on Socket angled M12, coding: A, cable length: 0.6 m

Commercial data

Item number	1505180
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	AF1CCA
GTIN	4017918902360
Weight per piece (including packing)	68 g
Weight per piece (excluding packing)	68 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable



1505180

<https://www.phoenixcontact.com/us/products/1505180>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug angled M12
Number of positions	4
Coding type	A

Connection 2

Type	Socket angled M12
------	-------------------

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable



1505180

<https://www.phoenixcontact.com/us/products/1505180>

Number of positions	4
Coding type	A

Cable/line

Cable length	0.6 m
--------------	-------

PUR/PVC green [350]

Number of positions	4
Shielded	no
Cable type	PUR/PVC green [350]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor cross section	0.5 mm ²
External cable diameter	7.8 mm
Outer sheath, material	PUR
External sheath, color	green RAL 6017
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown-white, green-yellow
Thickness, insulation	Core insulation approx. 1.00 mm (Inner sheath) approx. 0.70 mm (Outer cable sheath)
Nominal voltage, cable	300 V
Test voltage	1500 V
Smallest bending radius, movable installation	78 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 78 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67 IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket) -40 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)


SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable

1505180

<https://www.phoenixcontact.com/us/products/1505180>


Drawings

Dimensional drawing



M12 x 1 male plug, angled

Dimensional drawing



M12 x 1 socket, angled

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable

1505180

<https://www.phoenixcontact.com/us/products/1505180>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable

1505180


<https://www.phoenixcontact.com/us/products/1505180>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable



1505180

<https://www.phoenixcontact.com/us/products/1505180>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

SAC-4P-M12MR/ 0,6-PUR/M12FR TP - Sensor/actuator cable



1505180

<https://www.phoenixcontact.com/us/products/1505180>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com