

UC-12SDN8A80AA - Cable connector



1607071

<https://www.phoenixcontact.com/us/products/1607071>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, shielded: yes, cable diameter range: 10 mm ... 10 mm, connection method: Crimp connection, series: UC

Commercial data

Item number	1607071
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIA
GTIN	4046356259521
Weight per piece (including packing)	87.06 g
Weight per piece (excluding packing)	87.06 g
Country of origin	DE

UC-12SDN8A80AA - Cable connector



1607071

<https://www.phoenixcontact.com/us/products/1607071>

Technical data

Product properties

Series	UC
Application	Feedback
Connection profile	12
Shielded	yes
Thread type	M23

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	150 V

Connection data

Connection method	Crimp connection
-------------------	------------------

Connector

Type	straight
------	----------

Cable/line

External cable diameter	10 mm ... 10 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com