

FLKM-D37 SUB/S/FL/V/SO91 - Termination board



2283045

<https://www.phoenixcontact.com/us/products/2283045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module, with screw connection and D-SUB miniature pin strip, for mounting on NS 35/7.5 or NS 32, 37-pos.

Commercial data

Item number	2283045
Packing unit	1 pc
Minimum order quantity	20 pc
Product key	DK2A82
GTIN	4017918245986
Weight per piece (including packing)	188.61 g
Weight per piece (excluding packing)	2.05 g
Country of origin	DE

FLKM-D37 SUB/S/FL/V/SO91 - Termination board



2283045

<https://www.phoenixcontact.com/us/products/2283045>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE

Electrical properties

Nominal voltage U_N	25 V AC
	60 V DC

Connection data

Connection method	Screw connection
Connection method	D-SUB pin strip
Number of positions	37

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------