

CRIMPFOX 6-M - Crimping pliers



1212720

<https://www.phoenixcontact.com/us/products/1212720>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

Your advantages

- Unlockable pressure lock
- Marked die stations for precise processing of corresponding cross sections
- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Consistently high crimping quality

Commercial data

Item number	1212720
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356857796
Weight per piece (including packing)	628 g
Weight per piece (excluding packing)	628 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX 6-M - Crimping pliers



1212720

<https://www.phoenixcontact.com/us/products/1212720>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp
Product property	Unlockable pressure lock
	Marked die stations
	Optimized leverage

Crimping position 1

Min. cross section	0.25 mm ²
Max. cross section	0.75 mm ²
AWG min	24
AWG max	20

Crimping position 2

Min. cross section	1 mm ²
Max. cross section	1.5 mm ²
AWG min	18
AWG max	16

Crimping position 3

Max. cross section	2.5 mm ²
AWG max	14

Crimping position 4

Max. cross section	4 mm ²
AWG max	12

Crimping position 5

Max. cross section	6 mm ²
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 6 mm ²
Cross section range AWG	24 ... 10

Dimensions

Width	22 mm
-------	-------

CRIMPFOX 6-M - Crimping pliers

1212720

<https://www.phoenixcontact.com/us/products/1212720>



Height	76 mm
Length	204 mm

Material specifications

Color	black
-------	-------

CRIMPFOX 6-M - Crimping pliers

1212720

<https://www.phoenixcontact.com/us/products/1212720>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212720>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 6-M - Crimping pliers



1212720

<https://www.phoenixcontact.com/us/products/1212720>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 6-M - Crimping pliers



1212720

<https://www.phoenixcontact.com/us/products/1212720>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com