

# NBC-MSD/3,8-937/R4AQ AE7 FI - Network cable



1415851

<https://www.phoenixcontact.com/us/products/1415851>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), 4-pos., RADOX® GKW, RAL 9005 (black), shielded, straight M12 SPEEDCON/IP67 connector (D-coding) to straight RJ45/IP20 QUICKON connector, cable length: 3.8 m, customer version

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1415851       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 50 pc         |
| Product key                          | AF1CJN        |
| GTIN                                 | 4055626053691 |
| Weight per piece (including packing) | 281.7 g       |
| Weight per piece (excluding packing) | 281.7 g       |
| Country of origin                    | PL            |

1415851

<https://www.phoenixcontact.com/us/products/1415851>

Technical data

Product properties

|              |                         |
|--------------|-------------------------|
| Product type | Data cable preassembled |
|--------------|-------------------------|

Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 48 V AC |
|                       | 60 V DC |

Classifications

ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|