

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable

1534067
<https://www.phoenixcontact.com/us/products/1534067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR, gray RAL 7001, shielded, free cable end, on Socket straight M12, coding: A, cable length: 5 m

Commercial data

Item number	1534067
Packing unit	5 pc
Minimum order quantity	50 pc
Product key	AF1CMA
GTIN	4017918993566
Weight per piece (including packing)	461.9 g
Weight per piece (excluding packing)	461.9 g
Country of origin	PL

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable



1534067

<https://www.phoenixcontact.com/us/products/1534067>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	2 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M12
Number of positions	8
Coding type	A

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable



1534067

<https://www.phoenixcontact.com/us/products/1534067>

Cable/line

Cable length	5 m
PUR/PVC shielded, gray [100 TP]	
Cable weight	72 kg/km
Number of positions	8
Shielded	yes
Cable type	PUR/PVC shielded, gray [100 TP]
Conductor structure signal line	32x 0.10 mm (Signal line)
AWG signal line	24
Conductor structure, voltage supply	32x 0.10 mm (Drain wire)
Conductor cross section	4x 2x 0.25 mm ² (twisted pair)
	1x 0.25 mm ² (Drain wire)
Wire diameter incl. insulation	1.3 mm ±0.05 mm
External cable diameter	7.6 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	white-brown, green-yellow, gray-pink, blue-red
Thickness, insulation	0.33 mm (Core insulation)
	0.80 mm (Outer cable sheath)
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	Wires twisted in pair
Optical shield covering	82 %
Insulation resistance	≥ 100 MΩ*km
Working capacitance	100 pF (Line-line)
	145 pF (Line-shield)
Nominal voltage, cable	250 V
Test voltage Core/Core	1500 V
Test voltage Core/Shield	1500.00 V
Smallest bending radius, fixed installation	76 mm
Smallest bending radius, movable installation	76 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 76 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable



1534067

<https://www.phoenixcontact.com/us/products/1534067>

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable

1534067

<https://www.phoenixcontact.com/us/products/1534067>


Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable



1534067

<https://www.phoenixcontact.com/us/products/1534067>

Classifications

ECLASS

ECLASS-15.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-8P- 5,0-100/M12FS SH TP - Sensor/actuator cable



1534067

<https://www.phoenixcontact.com/us/products/1534067>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com