

RC-12S8N1280U1 - Cable connector



1600412

<https://www.phoenixcontact.com/us/products/1600412>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, straight, Screw locking mechanism, cable diameter range: 9.5 mm ... 10.5 mm

Commercial data

Item number	1600412
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356879170
Weight per piece (including packing)	66.93 g
Weight per piece (excluding packing)	66.93 g
Country of origin	DE

RC-12S8N1280U1 - Cable connector



1600412

<https://www.phoenixcontact.com/us/products/1600412>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Housing	
Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65
	IP67
	IP68

Seal	
External cable diameter	9.5 mm ... 10.5 mm
Seal material	NBR

RC-12S8N1280U1 - Cable connector



1600412

<https://www.phoenixcontact.com/us/products/1600412>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com