

VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector



1608016

<https://www.phoenixcontact.com/us/products/1608016>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, color: silver, Ethernet

Commercial data

Item number	1608016
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
GTIN	4046356131681
Weight per piece (including packing)	70.9 g
Weight per piece (excluding packing)	67.24 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252
---------	--

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance	0.001 Ω (Wire – IDC) 0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

Connection data

Connection technology	
Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
Conductor cross section	0.13 mm ² ... 0.32 mm ² (solid) 0.14 mm ² ... 0.36 mm ² (flexible)

Dimensions

Width	22 mm
Height	30 mm

VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector



1608016

<https://www.phoenixcontact.com/us/products/1608016>

Length	72 mm
--------	-------

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Seal material, pin connector pattern	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	CuZn

Cable/line

External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm ²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 250
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 45 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector



1608016

<https://www.phoenixcontact.com/us/products/1608016>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1608016>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	50 V	1.75 A	- 22	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	50 V	1.75 A	- 22	-

VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector



1608016

<https://www.phoenixcontact.com/us/products/1608016>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440290

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector



1608016

<https://www.phoenixcontact.com/us/products/1608016>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	6ecc2b5f-8b5a-45ae-a6a1-6ca00e65005d

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com