

SB-10KP002 - Crimp contact



1623611
<https://www.phoenixcontact.com/us/products/1623611>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Pin, turned, contact diameter: 1 mm, connection cross section: 0.34 mm² ... 0.5 mm², contact material: CuZn

Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

Commercial data

Item number	1623611
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB36
Product key	ABREAD
GTIN	4055626285917
Weight per piece (including packing)	0.488 g
Weight per piece (excluding packing)	0.46 g
Customs tariff number	85366990
Country of origin	DE

SB-10KP002 - Crimp contact

1623611

<https://www.phoenixcontact.com/us/products/1623611>



Technical data

Product properties

Product type	Crimp contact
Contact material type	turned

Connection data


Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Connection cross section	0.34 mm² ... 0.5 mm²

Material specifications

Material Contact	CuZn
Material Metal surface contact area (middle layer)	Ni
Material Metal surface contact area (top layer)	Au

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1 mm

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	100

SB-10KP002 - Crimp contact


1623611

<https://www.phoenixcontact.com/us/products/1623611>



Drawings

Dimensional drawing



Dimensional drawing

SB-10KP002 - Crimp contact



1623611

<https://www.phoenixcontact.com/us/products/1623611>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

SB-10KP002 - Crimp contact



1623611

<https://www.phoenixcontact.com/us/products/1623611>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0605a2e8-1331-41f8-aed6-d106f053653c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com