

DP-UKK 3-MSTB-5,08 - Spacer plate



2770600

<https://www.phoenixcontact.com/us/products/2770600>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer plate, to compensate for level offsets, pitch: 5.08 mm, width: 2.5 mm, height: 50 mm, number of positions: 1, color: gray



Commercial data

Item number	2770600
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4017918067984
Weight per piece (including packing)	1.748 g
Weight per piece (excluding packing)	1.684 g
Customs tariff number	39269097
Country of origin	DE

DP-UKK 3-MSTB-5,08 - Spacer plate



2770600

<https://www.phoenixcontact.com/us/products/2770600>

Technical data

Product properties

Product type	Partition plate
Product family	DECKEL + RZ + DP
Number of positions	1
Pitch	5.08 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	2.5 mm
Height	50 mm
Pitch	5.08 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

DP-UKK 3-MSTB-5,08 - Spacer plate



2770600

<https://www.phoenixcontact.com/us/products/2770600>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DP-UKK 3-MSTB-5,08 - Spacer plate



2770600

<https://www.phoenixcontact.com/us/products/2770600>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com