

# FUSE-10X38-16A-GR - Fuse

2903126

<https://www.phoenixcontact.com/us/products/2903126>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 16 A, tripping characteristic: super-fast blow (gR)

## Commercial data

Item number	2903126
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C470
Product key	DK7455
GTIN	4046356713313
Weight per piece (including packing)	8 g
Weight per piece (excluding packing)	8 g
Customs tariff number	85361050
Country of origin	FR

# FUSE-10X38-16A-GR - Fuse

2903126

<https://www.phoenixcontact.com/us/products/2903126>



## Technical data

### Product properties

Product type	Fuse
Number of fuses in the set	10

### Electrical properties

Tripping characteristic	super-fast blow (gR)
Maximum power dissipation for nominal condition	3 W
Nominal voltage $U_N$	690 V
Nominal current $I_N$	16 A
Fuse rating	CC
Fuse	Fuse

### Dimensions

Dimensions	10 x 38 mm
------------	------------

# FUSE-10X38-16A-GR - Fuse

2903126

<https://www.phoenixcontact.com/us/products/2903126>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903126>



**EAC**

Approval ID: RU C-DE.BL08.B.00724

# FUSE-10X38-16A-GR - Fuse



2903126

<https://www.phoenixcontact.com/us/products/2903126>

## Classifications

### ECLASS

ECLASS-13.0	27142002
ECLASS-13.0	27142002

### ETIM

ETIM 9.0	EC002704
----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# FUSE-10X38-16A-GR - Fuse



2903126

<https://www.phoenixcontact.com/us/products/2903126>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)