

# MARKING BOX HU HU - Thermal transfer printer set



0801750

<https://www.phoenixcontact.com/us/products/0801750>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Printing set**, consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x THERMOMARK CARD, Order No. 5146464, 1 x MARKING NOTEBOOK (without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL, country-specific keyboard version and operating system

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0801750       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | BG1222        |
| GTIN                                 | 4046356694957 |
| Weight per piece (including packing) | 16,720.87 g   |
| Weight per piece (excluding packing) | 14,920.8 g    |
| Country of origin                    | DE            |

# MARKING BOX HU HU - Thermal transfer printer set



0801750

<https://www.phoenixcontact.com/us/products/0801750>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Marking system |
|--------------|----------------|

### Device properties

|                  |                                             |
|------------------|---------------------------------------------|
| Print resolution | 300 dpi                                     |
| Operating system | MS Windows 7, MS Windows 8.1, MS Windows 10 |

### Electrical properties

#### Supply

|                      |                                         |
|----------------------|-----------------------------------------|
| Supply voltage range | 100 V AC ... 240 V AC (50 Hz ... 60 Hz) |
|----------------------|-----------------------------------------|

### Dimensions

|       |        |
|-------|--------|
| Width | 785 mm |
|-------|--------|

### Material specifications

|       |      |
|-------|------|
| Color | gray |
|-------|------|

### Environmental and real-life conditions

#### Ambient conditions

|                                  |                |
|----------------------------------|----------------|
| Ambient temperature (operation)  | 5 °C ... 35 °C |
| Permissible humidity (operation) | 10 % ... 80 %  |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)