

# ZB 15/RD-100:UNPRINTED - Zack marker strip



0815237

<https://www.phoenixcontact.com/us/products/0815237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, red, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap in, for terminal block width: 15.2 mm, Number of individual labels: 500

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0815237       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Product key                          | BG2112        |
| GTIN                                 | 4046356073561 |
| Weight per piece (including packing) | 3.336 g       |
| Weight per piece (excluding packing) | 3.126 g       |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Klemmenmarker |
| Pitch        | 15.2 mm       |

### Marking

|                                     |     |
|-------------------------------------|-----|
| Number of individual labels         | 500 |
| Number of individual labels per row | 5   |
| Number of marker strips             | 100 |

### Dimensions

|        |          |
|--------|----------|
| Width  | 15.10 mm |
| Height | 10.50 mm |
| Depth  | 4.20 mm  |
| Pitch  | 15.2 mm  |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | red (RAL 3001)                 |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |         |
|---------------|---------|
| Mounting type | snap in |
|---------------|---------|

# ZB 15/RD-100:UNPRINTED - Zack marker strip



0815237

<https://www.phoenixcontact.com/us/products/0815237>

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)