

C-MEA 6/3 - Operating lever



1394609

<https://www.phoenixcontact.com/in/products/1394609>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Operating lever, depth: 24.4 mm, width: 24.4 mm, height: 15.9 mm, number of positions: 3, color: orange

Commercial data

Item number	1394609
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE2ZWX
GTIN	4063151777425
Weight per piece (including packing)	2.47 g
Weight per piece (excluding packing)	2.47 g
Country of origin	PL

C-MEA 6/3 - Operating lever

1394609

<https://www.phoenixcontact.com/in/products/1394609>



Technical data

Product properties

Product type	Switch module
Number of positions	3

Dimensions

Width	24.4 mm
Height	15.9 mm
Depth	24.4 mm

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

C-MEA 6/3 - Operating lever

1394609

<https://www.phoenixcontact.com/in/products/1394609>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250392

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

C-MEA 6/3 - Operating lever



1394609

<https://www.phoenixcontact.com/in/products/1394609>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in