

# H1X:D1MF - Housing

1415765

<https://www.phoenixcontact.com/us/products/1415765>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYPORT B6 panel mounting base, with single locking latch, with plastic protective cover, with stainless steel front plate connections, 1x D-SUB 9 (male/female)

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1415765
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF69
Product key	AF7EGX
GTIN	4055626804392
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	US

## Technical data


### Product properties

Product type	Stackable housing set
Housing type	Panel mounting base
Application	Standard
Type	B6
Protective cover	yes

### Connection data

Tightening torque	1.5 ... 2 Nm
-------------------	--------------

### Dimensions

Dimensional drawing	
Width	53 mm
Height	30.5 mm
Length	80.5 mm
Drill hole distance, horizontal	70 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

### Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	52 mm

### Material specifications

Material	Stainless steel (Front plate)
Seal material	NBR, conductive
	NBR, conductive
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Material, protective cover	PA
Locking latch material	Polyamide

### Connector

Contact insert design	with 1x D-SUB 9 pin/Terminal block slot locking #4-40 UNC bolts
-----------------------	---

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
	IP67

# H1X:D1MF - Housing

1415765

<https://www.phoenixcontact.com/us/products/1415765>



Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C (Housing)

# H1X:D1MF - Housing


1415765

<https://www.phoenixcontact.com/us/products/1415765>




## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout

# H1X:D1MF - Housing

1415765

<https://www.phoenixcontact.com/us/products/1415765>



## Classifications

### ECLASS

ECLASS-15.0	27440113
ECLASS-13.0	27440113

### ETIM

ETIM 9.0	EC002636
----------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------