

1426130

<https://www.phoenixcontact.com/us/products/1426130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 3-position, PUR, black, free cable end, on Socket angled M12, coding: S, Customer version

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special S-coding

Commercial data

Item number	1426130
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	AF1CBB
GTIN	4055626447360
Weight per piece (including packing)	441.2 g
Weight per piece (excluding packing)	430.6 g
Country of origin	PL

SAC-3P-5,6PUR/FRS PEPPH2,5 DMG - Power cable



1426130

<https://www.phoenixcontact.com/us/products/1426130>

Technical data

Product properties

Product type	Power cable
Application	Energy supply
Number of positions	3
No. of cable outlets	1
Coding	S

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
--	----

Electrical properties

Nominal voltage U_N	230 V AC
	230 V DC
Nominal current I_N	12 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket angled M12
Coding type	S (Power)

Cable/line

Number of positions	3
Shielded	no
Outer sheath, material	PUR
External sheath, color	black


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67 (without preloading, as additional test in accordance with IEC 60529)

Drawings

Dimensional drawing




M12 x 1 socket, angled

1426130

<https://www.phoenixcontact.com/us/products/1426130>

Schematic diagram



Pin assignment of M12 socket, 3-pos., S-coded, socket side view

SAC-3P-5,6PUR/FRS PEPPH2,5 DMG - Power cable



1426130

<https://www.phoenixcontact.com/us/products/1426130>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1426130>

 UL Listed Approval ID: FILE E 468743				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	300 V	12 A	- 16	- 16

 cUL Listed Approval ID: FILE E 468743				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	300 V	12 A	- 16	-

SAC-3P-5,6PUR/FRS PEPPH2,5 DMG - Power cable



1426130

<https://www.phoenixcontact.com/us/products/1426130>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-5,6PUR/FRS PEPPH2,5 DMG - Power cable



1426130

<https://www.phoenixcontact.com/us/products/1426130>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com