

VS-15-BU-DSUB-FK - D-SUB contact insert



1688900

<https://www.phoenixcontact.com/us/products/1688900>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB contact insert, shell size 2, with 15 signal contacts, type of contact socket, flat-ribbon cable connection, angled, fixing with a 3 mm hole, for panel mounting frame VS-15-...

Your advantages

- D-SUB 15 connection
- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

Commercial data

Item number	1688900
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918823054
Weight per piece (including packing)	14.13 g
Weight per piece (excluding packing)	11.42 g
Customs tariff number	85366990
Country of origin	DE

VS-15-BU-DSUB-FK - D-SUB contact insert



1688900

<https://www.phoenixcontact.com/us/products/1688900>

Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB
Number of slots	1
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	1.5 A (at 20 °C)
Test voltage	1000 V
Transmission medium	Copper
Power transmission	Power

Connection data

Connection method	Flat-ribbon cable connection
-------------------	------------------------------

Dimensions

Width	18.5 mm
Height	12.93 mm
Length	39.52 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	Polyester GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

Environmental and real-life conditions

VS-15-BU-DSUB-FK - D-SUB contact insert



1688900

<https://www.phoenixcontact.com/us/products/1688900>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-15-BU-DSUB-FK - D-SUB contact insert



1688900

<https://www.phoenixcontact.com/us/products/1688900>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-15-BU-DSUB-FK - D-SUB contact insert



1688900
<https://www.phoenixcontact.com/us/products/1688900>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com