

# EB 2-CC 7,5 - Insertion bridge

1948048

<https://www.phoenixcontact.com/us/products/1948048>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 7.5 mm, number of positions: 2, length: 17 mm, color: gray



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1948048       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE19          |
| Product key                          | BE1Z2X        |
| GTIN                                 | 4017918918668 |
| Weight per piece (including packing) | 0.997 g       |
| Weight per piece (excluding packing) | 0.957 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# EB 2-CC 7,5 - Insertion bridge

1948048

<https://www.phoenixcontact.com/us/products/1948048>



## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Insertion bridge |
| Number of positions | 2                |
| Pitch               | 7.5 mm           |

### Dimensions

|        |         |
|--------|---------|
| Width  | 11.7 mm |
| Height | 16.5 mm |
| Length | 16.5 mm |
| Pitch  | 7.5 mm  |

### Material specifications

|          |                 |
|----------|-----------------|
| Color    | gray (RAL 7042) |
| Material | PA              |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C                                                         |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

# EB 2-CC 7,5 - Insertion bridge

1948048

<https://www.phoenixcontact.com/us/products/1948048>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000489 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# EB 2-CC 7,5 - Insertion bridge



1948048  
<https://www.phoenixcontact.com/us/products/1948048>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)