

PSD-S OE LED RFL BU - Optical element



2700135

<https://www.phoenixcontact.com/us/products/2700135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED random flashing beacon element, 24 V DC, blue

Your advantages

- Tool-free element changeover
- High light and color intensity
- Can be freely combined
- Minimum LED service life of 50,000 h
- Low power consumption
- Random flashing light prevents familiarization effect
- Degree of protection IP65

Commercial data

Item number	2700135
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL112
GTIN	4046356491273
Weight per piece (including packing)	82 g
Weight per piece (excluding packing)	78 g
Customs tariff number	85318070
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties


Product type	Signal element
Product family	PSD-S
Area of application	Signal tower

Electrical properties

General

Input voltage	24 V DC
Maximum inrush current	max. 500 mA
Current consumption	typ. 35 mA
Source of light type	LED
Operating time	100 %
Service life electrical	max. 50,000 h
Optical signal type	LED random flashing beacon (RLF)

Dimensions

Dimensional drawing	
Height	65.5 mm
Diameter	70 mm

Material specifications

Calotte color	blue
Material	Polycarbonate PC

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (when installed or with end cover)
Ambient temperature (operation)	-20 °C ... 50 °C

PSD-S OE LED RFL BU - Optical element



2700135

<https://www.phoenixcontact.com/us/products/2700135>

EMC data


Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Mounting

Mounting type	Plug-in mounting (Seal pre-installed for each element)
Mounting position	any

Drawings

Dimensional drawing



PSD-S OE LED RFL BU - Optical element



2700135

<https://www.phoenixcontact.com/us/products/2700135>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700135>



cULus Listed

Approval ID: E123528

PSD-S OE LED RFL BU - Optical element



2700135

<https://www.phoenixcontact.com/us/products/2700135>

Classifications

ECLASS

ECLASS-13.0	27371220
-------------	----------

ETIM

ETIM 9.0	EC000232
----------	----------

UNSPSC

UNSPSC 21.0	46171600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f5953d22-e25a-4164-bb5a-03665b2b7829