

IAK 16 - Branch terminal



2715982

<https://www.phoenixcontact.com/us/products/2715982>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Branch terminal, nominal current: 57 A, connection method: Screw connection, cross section: 0.5 mm² - 16 mm², color: gray

Commercial data

Item number	2715982
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE73
Product key	BE7331
GTIN	4017918061739
Weight per piece (including packing)	13.261 g
Weight per piece (excluding packing)	13.126 g
Customs tariff number	85369010
Country of origin	PL

Technical data

Product properties

Product type	Pick-off terminal
Number of rows	1

Electrical properties

Maximum load current	76 A
Maximum power dissipation for nominal condition	0 W
Nominal current I_N	57 A

Connection data

Maximum load current	76 A
Connection method	Screw connection
Screw thread	M4
Conductor cross-section rigid	0.5 mm ² ... 16 mm ²
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 10 mm ²
Conductor cross-section, flexible [AWG]	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²
2 conductors with same cross section, solid	0.5 mm ² ... 10 mm ²
2 conductors with same cross section, flexible	0.5 mm ² ... 10 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.5 mm ² ... 10 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 10 mm ²
Nominal current	57 A
Maximum load current	76 A (with 16 mm ² conductor cross-section)

Dimensions

Width	7.7 mm
Height	22.9 mm
Depth	28 mm
Length	22.9 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

IAK 16 - Branch terminal

2715982

<https://www.phoenixcontact.com/us/products/2715982>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2715982>



EAC

Approval ID: KZ7500651131219505

IAK 16 - Branch terminal



2715982

<https://www.phoenixcontact.com/us/products/2715982>

Classifications

ECLASS

ECLASS-13.0	27250116
ECLASS-15.0	27250116

ETIM

ETIM 9.0	EC000001
----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

IAK 16 - Branch terminal



2715982
<https://www.phoenixcontact.com/us/products/2715982>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com