

DF-UP 6 - Flange cover

3060856

<https://www.phoenixcontact.com/us/products/3060856>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flange cover, snap onto the UP 6/... plugs, connection method: Screw connection, depth: 24.7 mm, width: 4.5 mm, height: 21 mm, color: gray

Your advantages

- For reliable screw connection between the plug and screw flange
- The flange covers can be snapped onto the plug housing later on

Commercial data

Item number	3060856
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4046356607766
Weight per piece (including packing)	1.713 g
Weight per piece (excluding packing)	1.713 g
Customs tariff number	85389099
Country of origin	CN

DF-UP 6 - Flange cover

3060856

<https://www.phoenixcontact.com/us/products/3060856>



Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA

Dimensions

Width	4.5 mm
Height	21 mm
Depth	24.7 mm

DF-UP 6 - Flange cover

3060856

<https://www.phoenixcontact.com/us/products/3060856>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DF-UP 6 - Flange cover

3060856

<https://www.phoenixcontact.com/us/products/3060856>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com