

# SD-WMS 3 (CH)R YE:J - Wire marking tag



0825667:J

<https://www.phoenixcontact.com/us/products/0825667:J>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the capital letter: J, yellow, mounting type: thread on

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0825667:J     |
| Packing unit                         | 500 pc        |
| Minimum order quantity               | 500 pc        |
| Product key                          | BG2221        |
| GTIN                                 | 4046356419536 |
| Weight per piece (including packing) | 0.06 g        |
| Weight per piece (excluding packing) | 0.028 g       |
| Country of origin                    | SE            |

# SD-WMS 3 (CH)R YE:J - Wire marking tag



0825667:J

<https://www.phoenixcontact.com/us/products/0825667:J>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|          |   |
|----------|---|
| Printing | J |
|----------|---|

### Dimensions

|        |         |
|--------|---------|
| Width  | 3.2 mm  |
| Height | 3.6 mm  |
| Length | 3.50 mm |

### External dimensions

|                  |                 |
|------------------|-----------------|
| Outside diameter | 1.3 mm ... 3 mm |
|------------------|-----------------|

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | yellow                         |
| Material                               | Polyvinyl chloride             |
| Flammability rating according to UL 94 | V0                             |
| Components                             | Free from silicone and cadmium |

### Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 1.3 mm ... 3 mm |
|-------------------------|-----------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 60 °C |
|---------------------------------|------------------|

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |           |
|---------------|-----------|
| Mounting type | thread on |
|---------------|-----------|

# SD-WMS 3 (CH)R YE:J - Wire marking tag



0825667:J

<https://www.phoenixcontact.com/us/products/0825667:J>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)