

CRIMPFOX CENTRUS 10H - Crimping pliers



1213156

<https://www.phoenixcontact.com/us/products/1213156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² .. 10 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

Commercial data

Item number	1213156
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4055626212630
Weight per piece (including packing)	465.38 g
Weight per piece (excluding packing)	381.7 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX CENTRUS 10H - Crimping pliers



1213156

<https://www.phoenixcontact.com/us/products/1213156>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	HEX crimp
Product property	Unlockable pressure lock
	Low grip span
	Up to 30% lower actuation force
	Protection against damage caused by dropping, thanks to sturdy plastic guard over the pliers head

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	26
AWG max	8

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 10 mm ² (2 x 0.5 mm ² ... 2 x 4 mm ²)
Cross section range AWG	26 ... 8 (2 x AWG 20 ... 2 x AWG 12)

Dimensions

Width	70 mm
Height	21 mm
Length	180 mm

Material specifications

Color	black/green
-------	-------------

CRIMPFOX CENTRUS 10H - Crimping pliers



1213156

<https://www.phoenixcontact.com/us/products/1213156>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213156>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 10H - Crimping pliers



1213156

<https://www.phoenixcontact.com/us/products/1213156>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX CENTRUS 10H - Crimping pliers



1213156
<https://www.phoenixcontact.com/us/products/1213156>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com