

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR, black RAL 9005, Plug straight M8, coding: A, on Socket straight M8, coding: A, cable length: 0.8 m

Commercial data

Item number	1508747
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1BBA
GTIN	4017918897680
Weight per piece (including packing)	30.01 g
Weight per piece (excluding packing)	30.01 g
Country of origin	PL

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M8
Number of positions	3
Coding type	A

Connection 2

Type	Socket straight M8
Number of positions	3
Coding type	A

Cable/line

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Cable length	0.8 m
PUR black, permanently flexible control cable [300]	
Number of positions	3
Shielded	no
Cable type	PUR black, permanently flexible control cable [300]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	0.25 mm²
External cable diameter	4.7 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Nominal voltage, cable	300 V
Test voltage	1500 V
Smallest bending radius, movable installation	47 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 47 mm, Traversing path: 2 m, Traversing rate: 2 m/s
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable

1508747

<https://www.phoenixcontact.com/us/products/1508747>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




Socket M8 x 1, straight

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable

1508747


<https://www.phoenixcontact.com/us/products/1508747>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side


SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Circuit diagram



Contact assignment of M8 plugs/sockets

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-3P-M 8MS/ 0,8-300/M 8FS - Sensor/actuator cable



1508747

<https://www.phoenixcontact.com/us/products/1508747>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com