

RC-09S2N224000 - Device connector rear mounting



1596699

<https://www.phoenixcontact.com/us/products/1596699>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, series: RC, straight, Screw locking mechanism, Flat gasket. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1596699
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFR
GTIN	4046356212229
Weight per piece (including packing)	30.806 g
Weight per piece (excluding packing)	30.806 g
Country of origin	DE

RC-09S2N224000 - Device connector rear mounting



1596699

<https://www.phoenixcontact.com/us/products/1596699>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder-in connection
-------------------	----------------------

Connector

Housing

Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M2,5)
Material (Housing)	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------


Drawings

Dimensional drawing



Dimensional drawing


Dimensional drawing



Dimensional drawing

1596699

<https://www.phoenixcontact.com/us/products/1596699>



Installation dimensions

RC-09S2N224000 - Device connector rear mounting



1596699

<https://www.phoenixcontact.com/us/products/1596699>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a1c272d8-df25-4762-b574-c43f2b0513b0