

# KGG-MSTB 2,5/ 4 GY - Cable housing

1702452

<https://www.phoenixcontact.com/us/products/1702452>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable housing, product range: KGG-MSTB 2,5, width: 19 mm

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1702452                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | AAHZDC                         |
| GTIN                                 | 4046356586665                  |
| Weight per piece (including packing) | 7.4 g                          |
| Weight per piece (excluding packing) | 7.27 g                         |
| Country of origin                    | PL                             |

# KGG-MSTB 2,5/ 4 GY - Cable housing



1702452

<https://www.phoenixcontact.com/us/products/1702452>

## Technical data

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Cable housing |
| Product family      | KGG-MSTB 2,5  |
| Number of positions | 4             |
| Pitch               | 0 mm          |

### Mounting

#### Cable clamp

|                   |        |
|-------------------|--------|
| Tightening torque | 0.2 Nm |
|-------------------|--------|

### Material specifications

|                                        |     |
|----------------------------------------|-----|
| Flammability rating according to UL 94 | HB  |
| Insulating material                    | ABS |
| Insulating material group              | I   |
| CTI according to IEC 60112             | 600 |
| Flammability rating according to UL 94 | HB  |

### Dimensions

|        |       |
|--------|-------|
| Width  | 19 mm |
| Height | 37 mm |
| Pitch  | -     |

# KGG-MSTB 2,5/ 4 GY - Cable housing



1702452

<https://www.phoenixcontact.com/us/products/1702452>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460402 |
| ECLASS-15.0 | 27460402 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# KGG-MSTB 2,5/ 4 GY - Cable housing



1702452

<https://www.phoenixcontact.com/us/products/1702452>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)