

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cross connection rail, for fixed bridging of identical inputs and outputs, made of Cu, nickel-plated, 1 m long

Commercial data

Item number	0201595
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918098971
Weight per piece (including packing)	55 g
Weight per piece (excluding packing)	55 g
Customs tariff number	85369095
Country of origin	DE

Technical data

Product properties

Product type	Bridge
Pitch	31 mm

Electrical properties

Maximum load current	30 A
----------------------	------

Connection data

Maximum load current	30 A
----------------------	------

Dimensions

Pitch	31 mm
-------	-------

Material specifications

Color	silver-colored
Material	Copper
Coating	tin-plated

Mounting

Mounting type	Screw mounting
---------------	----------------

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com