

# DS-PT 2,5-QUATTRO-MT-R/500 - Cover segment

1085345

<https://www.phoenixcontact.com/us/products/1085345>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover segment, depth: 12.6 mm, width: 2.8 mm, height: 28.7 mm, color: gray



## Commercial data

Item number	1085345
Packing unit	500 pc
Minimum order quantity	500 pc
Product key	BE224Z
GTIN	4055626873510
Weight per piece (including packing)	0.315 g
Weight per piece (excluding packing)	0.299 g
Country of origin	PL

## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Width	2.8 mm
End cover width	2.8 mm
Height	28.7 mm
Depth	12.6 mm

### Notes

General	A cover segment should be used if terminal blocks with a higher number of terminal points cannot be covered by the contour of another terminal block.
---------	---

## Classifications

### ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DS-PT 2,5-QUATTRO-MT-R/500 - Cover segment

1085345

<https://www.phoenixcontact.com/us/products/1085345>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)