

IOA MCR-CJC-PT100 - Plug

1085776

<https://www.phoenixcontact.com/us/products/1085776>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug for cold junction compensation for thermocouples, in combination with MACX MCR(-EX)-TC... temperature transducers

Commercial data

Item number	1085776
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C402
Product key	DK111Z
GTIN	4055626875811
Weight per piece (including packing)	6.3 g
Weight per piece (excluding packing)	6.3 g
Customs tariff number	85332100
Country of origin	DE

IOA MCR-CJC-PT100 - Plug



1085776

<https://www.phoenixcontact.com/us/products/1085776>

Technical data

Product properties

Product type	Plug
--------------	------

Approvals

Corrosive gas test	
Identification	ISA S71.04.2013 G3 Harsh Group A

IOA MCR-CJC-PT100 - Plug

1085776

<https://www.phoenixcontact.com/us/products/1085776>



Classifications

ECLASS

ECLASS-13.0	27210192
ECLASS-15.0	27210192

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------