

SI-FP-R1A-U1A - Front plate

1404499

<https://www.phoenixcontact.com/us/products/1404499>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Front plate with contact inserts, plastic with shroud, 1 x USB (socket/socket) type A; 1 x RJ45, 8-pos. metal, CAT5e (socket/socket)

Commercial data

Item number	1404499
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF70
Product key	AF7EDX
GTIN	4046356698412
Weight per piece (including packing)	66.7 g
Weight per piece (excluding packing)	53.1 g
Customs tariff number	85366990
Country of origin	CZ

SI-FP-R1A-U1A - Front plate



1404499

<https://www.phoenixcontact.com/us/products/1404499>

Technical data

Notes

Assembly note	Strain relief USB internal: cable tie
---------------	---------------------------------------

Product properties

Product type	Data front plate
Number of slots	2
Shielded	yes


Electrical properties

Rated voltage (III/3)	max. 42.4 V DC (RJ45, USB A, UL-Rating)
	max. 30 V AC (RJ45, USB A, UL-Rating)
	48 V AC/DC (USB A)
Rated current	1.5 A (USB A)
	175 mA (RJ45)
Transmission speed	max. 5 Gbps (USB-A 3.0)

Connection data

Tightening torque	0.8 ... 1 Nm
-------------------	--------------

Dimensions

Dimensional drawing	
Width	50.7 mm
Height	87.5 mm
Depth	60 mm

Material specifications

Material Front plate	PBT (Front plate)
----------------------	-------------------

Connector

Contact insert design	with 1x RJ45 Socket/socket, snap-in slot locking
	with 1x USB A 3.0 Socket/socket, snap-in slot locking

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C

SI-FP-R1A-U1A - Front plate

1404499

<https://www.phoenixcontact.com/us/products/1404499>



Mounting

Assembly note	suitable for all mounting frames
---------------	----------------------------------

SI-FP-R1A-U1A - Front plate


1404499

<https://www.phoenixcontact.com/us/products/1404499>



Drawings

Dimensional drawing



Dimensional drawing

SI-FP-R1A-U1A - Front plate



1404499

<https://www.phoenixcontact.com/us/products/1404499>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1404499>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



EAC
Approval ID: RU C-DE.A*30.B.01102

SI-FP-R1A-U1A - Front plate



1404499

<https://www.phoenixcontact.com/us/products/1404499>

Classifications

ECLASS

ECLASS-13.0	27182806
ECLASS-15.0	27182806

ETIM

ETIM 9.0	EC000456
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

SI-FP-R1A-U1A - Front plate

1404499

<https://www.phoenixcontact.com/us/products/1404499>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com