

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	1424459
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	AF7AFX
GTIN	4055626372884
Weight per piece (including packing)	310.4 g
Weight per piece (excluding packing)	310.4 g
Customs tariff number	85366990
Country of origin	CN

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Set consists of

HC-EVO-D25-HHFS-PL-BK - Housing

1411347

<https://www.phoenixcontact.com/us/products/1411347>



HC-EVO-D25-BWS-PLR-BK - Housing

1411344

<https://www.phoenixcontact.com/us/products/1411344>



Panel mounting base D25, with single locking latch, material: PA 6.6-FR, height: 26 mm, cable gland: none, protective cover: no, Standard, with flat gasket

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

HC-D-G-M25-PLRBK - Cable gland

1411351

<https://www.phoenixcontact.com/us/products/1411351>



EVO plastic cable gland with bayonet locking, for housing series D, size M25, cable diameter: 9 mm ... 17 mm.

HC-A16-I-PT-M - Contact insert

1585375

<https://www.phoenixcontact.com/us/products/1585375>



HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

HC-A16-I-PT-F - Contact insert

1585388

<https://www.phoenixcontact.com/us/products/1585388>



HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Technical data

Product properties

Product type	Connector set
Housing type	Complete housing
Type	D25
Number of positions	16
No. of cable outlets	1
Protective cover	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV
Rated current	16 A

Connection data

Connection method	Push-in connection
Connection technology	Push-in connection
Conductor cross section	0.14 mm ² ... 2.5 mm ² (applies to stranded conductors with ferrules) 0.14 mm ² ... 2.5 mm ² (applies to stranded conductors with ferrules)
Connection cross section AWG	26 ... 14

Dimensions

Installation dimensions

Width of the assembly cutout	24 mm
Length of the assembly cutout	74 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	PA
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Locking latch material	PA

Cable/line

External cable diameter	9 mm ... 17 mm
-------------------------	----------------

Environmental and real-life conditions

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Ambient conditions

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 100 °C


HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Drawings



Mounting cutout


HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Schematic diagram




Pin assignment, connection side, pin left, socket right

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>



Derating diagram

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424459>

DNV

Approval ID: TAE000037S

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Classifications

ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-EVO-A16PT-BWS-HH-M25-PLRBK - Connector set



1424459

<https://www.phoenixcontact.com/us/products/1424459>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com