

1426092

<https://www.phoenixcontact.com/us/products/1426092>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, free cable end, on Socket angled M12, coding: A, cable length: 30 m

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1426092                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Product key                          | AF1CBA                         |
| GTIN                                 | 4055626444413                  |
| Weight per piece (including packing) | 871.5 g                        |
| Weight per piece (excluding packing) | 871.5 g                        |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Stainless steel                             |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V AC                   |
|                       | 250 V DC                   |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |        |
|-------------------|--------|
| Tightening torque | 0.4 Nm |
|-------------------|--------|

### Connector

#### Connection 1

# SAC-3P-30,0-PVC/M12FR VA - Sensor/actuator cable



1426092

<https://www.phoenixcontact.com/us/products/1426092>

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|


## Connection 2

|                     |                   |
|---------------------|-------------------|
| Type                | Socket angled M12 |
| Number of positions | 3                 |
| Coding type         | A                 |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 30 m |
|--------------|------|

## PVC black [PVC]

|                                               |                                                                                     |
|-----------------------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing                           |  |
| Cable weight                                  | 40 kg/km                                                                            |
| UL AWM Style                                  | 2464 / 1729 (80°C/300 V)                                                            |
| Number of positions                           | 3                                                                                   |
| Shielded                                      | no                                                                                  |
| Cable type                                    | PVC black [PVC]                                                                     |
| Conductor structure signal line               | 19x 0.15 mm                                                                         |
| AWG signal line                               | 22                                                                                  |
| Conductor cross section                       | 3x 0.34 mm² (Signal line)                                                           |
| Wire diameter incl. insulation                | 1.26 mm ±0.05 mm                                                                    |
| External cable diameter                       | 4.30 mm ±0.2 mm                                                                     |
| Outer sheath, material                        | PVC                                                                                 |
| External sheath, color                        | black RAL 9005                                                                      |
| Conductor material                            | Bare Cu litz wires                                                                  |
| Material wire insulation                      | PVC                                                                                 |
| Single wire, color                            | brown, blue, black                                                                  |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)                                                         |
| Thickness, outer sheath                       | ≥ 0.76 mm                                                                           |
| Overall twist                                 | 3 wires, twisted                                                                    |
| Max. conductor resistance                     | max. 57 Ω/km (at 20 °C)                                                             |
| Insulation resistance                         | ≥ 100 MΩ*km (at 20 °C)                                                              |
| Nominal voltage, cable                        | ≤ 300 V                                                                             |
| Test voltage                                  | ≥ 2500 V                                                                            |
| Minimum bending radius, fixed installation    | 5 x D                                                                               |
| Minimum bending radius, flexible installation | 10 x D                                                                              |
| Smallest bending radius, fixed installation   | 22 mm                                                                               |
| Smallest bending radius, movable installation | 43 mm                                                                               |

# SAC-3P-30,0-PVC/M12FR VA - Sensor/actuator cable



1426092

<https://www.phoenixcontact.com/us/products/1426092>

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Flame resistance                | As per UL-Style 2464                            |
| Ambient temperature (operation) | -25 °C ... 80 °C (cable, fixed installation)    |
|                                 | -10 °C ... 80 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions


|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


## Drawings

Dimensional drawing




M12 x 1 socket, angled

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 socket

# SAC-3P-30,0-PVC/M12FR VA - Sensor/actuator cable



1426092

<https://www.phoenixcontact.com/us/products/1426092>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-3P-30,0-PVC/M12FR VA - Sensor/actuator cable



1426092

<https://www.phoenixcontact.com/us/products/1426092>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)