

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, PVC, black, 5-wire, color single wire: black 1, black 2, black 3, black 4, green/yellow, cable length: 100 m

Commercial data

Item number	1457445
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4046356617772
Weight per piece (including packing)	6,465 g
Weight per piece (excluding packing)	6,465 g
Customs tariff number	85444995
Country of origin	PL

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Technical data


Product properties

Product type	Cable by the meter
Application	Valve connector
Number of positions	5
Shielded	no

Cable/line

Cable length	100 m
--------------	-------

PVC, 0.75 mm², black [534]

Dimensional drawing	
Cable weight	70.9 kg/km
UL AWM Style	2464 (80°C/300 V)
Number of positions	5
Shielded	no
Cable type	PVC, 0.75 mm², black [534]
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Conductor cross section	5x 0.75 mm²
Wire diameter incl. insulation	1.7 mm ±0.1 mm
External cable diameter	6.20 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, black 3, black 4, green/yellow
Overall twist	5 cores, twisted
Max. conductor resistance	26 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km (at 20 °C)
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	31 mm
	DIN VDE 0482

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Flame resistance	DIN EN 50265-2-1
	in acc. to UL VW1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1457445>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Classifications

ECLASS

ECLASS-15.0	27061801
ECLASS-13.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-100,0-534/0,75 - Cable reel



1457445

<https://www.phoenixcontact.com/us/products/1457445>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com