

RC-17P1N8AWT00 - Device connector front mounting



1601627

<https://www.phoenixcontact.com/us/products/1601627>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, Screw locking mechanism, M23, number of positions: 17, contact connection type: Pin, Axial O-ring, 4x Ø 3.2, shielded: yes, cable diameter range: 0 mm ... 0 mm, connection method: Crimp connection, series: RC

Commercial data

Item number	1601627
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFL
GTIN	4046356235778
Weight per piece (including packing)	25.24 g
Weight per piece (excluding packing)	25.24 g
Country of origin	DE

1601627

<https://www.phoenixcontact.com/us/products/1601627>

Technical data

Notes

Order information:

Order crimp contacts Ø 1 mm separately

Product properties

Product type	Circular connectors (device side)
Series	RC
Application	Feedback
Connection profile	17
Shielded	yes
Thread type	M23

Electrical properties

Contact

Contact diameter	1 mm
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Crimp connection
Contact connection type	Pin

Connector

Type	straight
------	----------

Cable/line

External cable diameter	0 mm ... 0 mm
-------------------------	---------------

Classifications

ETIM

ETIM 8.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%