

RC-17P2Y120000 - Contact insert



1625980

<https://www.phoenixcontact.com/us/products/1625980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 17, contact connection type: Pin, Solder connection, series: NC, RC, RM, TU, UC

Commercial data

Item number	1625980
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356981019
Weight per piece (including packing)	8.37 g
Weight per piece (excluding packing)	8.37 g
Country of origin	DE

RC-17P2Y120000 - Contact insert



1625980

<https://www.phoenixcontact.com/us/products/1625980>

Technical data

Product properties

Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	17
Connection profile	17
Coding	Y

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Solder connection
-------------------	-------------------

Connector

Direction of rotation	Counter direction
-----------------------	-------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com