

1733541

<https://www.phoenixcontact.com/us/products/1733541>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, number of positions per row: 3, product range: GSMKDSP 1,5, pitch: 7.62 mm, screw head form: L Slotted, color: green, Pin layout: Linear pinning, Solder pin [P]: 3.5 mm, type of packaging: packed in cardboard

Commercial data

Item number	1733541
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AA12
Product key	AALFGD
GTIN	4017918231835
Weight per piece (including packing)	5.07 g
Weight per piece (excluding packing)	4.612 g
Customs tariff number	85369010
Country of origin	DE

GSMKDSPL 1,5/ 3-7,62 - PCB terminal block



1733541

<https://www.phoenixcontact.com/us/products/1733541>

Technical data

Product properties

Product type	Printed circuit board terminal
Product family	GSMKDSP 1,5
Type	PC terminal block can be aligned
Number of positions	3
Pitch	7.62 mm
Pin layout	Linear pinning

Electrical properties

Rated voltage (II/2)	1000 V
Rated voltage (III/2)	630 V
Rated surge voltage (II/2)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (III/3)	6 kV

Mounting

Mounting type	Wave soldering
Pin layout	Linear pinning
Drive form screw head	Slotted (L)

Material specifications

Color (Housing)	green (RAL 6021)
Contact surface	Tin Sn

Dimensions

Width	22.86 mm
Installed height	16 mm
Height	19.5 mm
Length of the solder pin	3.5 mm
Length	13.4 mm
Length of the solder pin	3.5 mm
Hole diameter	1.3 mm
Pitch	7.62 mm

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

GSMKDSPL 1,5/ 3-7,62 - PCB terminal block



1733541

<https://www.phoenixcontact.com/us/products/1733541>

Classifications

ECLASS

ECLASS-13.0	27460101
ECLASS-15.0	27460101

ETIM

ETIM 9.0	EC002643
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1733541
<https://www.phoenixcontact.com/us/products/1733541>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com